

Lens Evetar M12B5025 F2.5 f50mm 1/2"

Order Numbers


- 2000036380 (without IR cut filter)
- 2000036381 (with IR cut filter)



Key Features

- S-mount lens with optimum price/performance ratio
- 1/2" lens with fixed focal length of 50.0 mm and fixed iris of f/2.5
- Available with IR cut filter (for color cameras) or without IR cut filter (for mono cameras)

Technical Specifications	
Image Circle	1/2"
Focal Length	50.0 mm
Aperture	f/2.5
Iris Type	fixed
MOD	500 mm
Resolution	5 MP – 200 lp/mm
Angle of View (D / H / V)	9.3° / 6.2° / 4.5°
Back Focal Length	18.63 mm
Mount	M12x0.5-6g



(Dimensions in mm)