






REV	DESCRIPTION\PER REQUEST	DRAWN	DATE



RECOMMENDED
CABLE STRIPPING DIM'S



Cable:BELDEN 1855A



10	Ferrule	1	Brass	Nickel
9	Shell	1	Brass	Nickel
8	Gasket	1	Rubber	Black
7	Retaining ring	1	Brass	Nickel
6	Spring	1	Brass	Nickel
5	Washer	1	Brass	Nickel
4	Dielectric	1	Teflon	None
3	Pin	1	Phos Bronze	Gold
2	Body	1	Beryllium	Nickel
1	Body	1	Brass	Nickel
<i>NO</i>	<i>Description</i>	<i>Q'ty</i>	<i>Material</i>	<i>Finish</i>

PART NO.	HHD1855A
APPROVED	DATE 10/11/12
CHECKED	DATE 10/11/12
DRAWN	DATE 10/11/12
	<i>Kai</i>

* MAJOR DIMENSION			
UNLESS OTHERWISE NOTED TOLERANCES			
0.5-6	=±0.2		
6-30	=±0.4		
30-120	=±0.6		
120-315	=±1.0		
ANGLES=±1°			
SCALE	4/1	UNIT	mm

Bomar Interconnect Products, Inc	
TITLE	HD BNC CRIMP PLUG
DRAWING NO.	ASHDBNC-41004-G-75-TGN
REV	B
FILE NO. W:\AS\ASHDBNC\ASHDBNC-41004-G-75-TGN Bomar->20121005	