






OPTIONAL CONSTRUCTION 1
(ANTI-STICK RING)




OPTIONAL CONSTRUCTION 2
THIS IS THE PREFERRED CONSTRUCTION FOR NEW TOOL BUILDS
(ANTI-STICK RING)

SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	7	NO MISSING SYMBOL NUMBER
	LAST NO. USED	5	




DWG STATUS		ZONE		REVISION HISTORY		AUTH		DATE	
16ND999	R 001	-	-	REDRAWN TO PD		990009	JLZ/RCH	1	2
16ND999	R 002	-	-	15324993-97 - RELEASED		990005	JLZ/RCH	1	2
07ND000	R 003	-	-	15324993-97 - REVISED		202978	JLZ/EAR	1	2
07ND000	R 004	-	-	15397197 - RELEASED		000005	HH/EAR	1	2
15MR004	R 05	-	-	12052668 & 12052387 PER NIN EMO BOLTS: ALL PARTS - UPDATED MATERIAL SPEC		251587	HH/RH	1	2
18ND004	- 06	-	-	12052387 & 12052668 - REVISED DRAWING CHART: 12052668 - REVISED DIM "0"		261372	J5/J5	1	2
030006	R 07	-	-	ALL ACTIVE PARTS - ADDED SEALING RIBS VIEWS, OVERALL LENGTH LABEL, SEALING RIBS LABEL, ANTI-STICK RING OPTIONAL CONSTRUCTION 1 & 2 VIEWS AND DIMS (2 PLS); REMOVED OPTIONAL CONSTRUCTION VIEWS, CONSTRUCTION LINE VIEWS, TYPES 304-306 DIM Ø C FOR TYPE 302; COLUMNS F & G AND REVISED DIMS (2 PLS); 15324993-97 & 15397197 - MAT'L SPEC WAS W3466 & ADDED ALTERNATE MAT'L SPEC		285215	JBD/FRB	1	2
08JAO7	R 08	-	-	10730241, 15344951, 15344032 & 10730240 - ADDED PART NUMBERS AS MYLAR ASSEMBLIES		400035	JTV/FRB	1	2
24JL09	R 09	-	-	ALL PARTS - UPDATED MATERIAL CALLOUT		408462	ECB/AUG	1	2
15JN10	R 10	-	-	10730240, 41, 12059297-60, 12077760, 15344032 & 15344951 - MOVED TO SHEET 14; 12052387 & 12052668 - OBSOLETE AND ADDED "REPLACED BY" COLUMN ON CHART		411067	AGM/JAM	1	2




SEALING RIBS MUST BE FREE OF SINKS, VOIDS, KNIT LINES AND FLASH IN THE AREA SHOWN ALL AROUND PART.
SEE VPS A-121 FOR ADDITIONAL INFORMATION.

0.15


0.15




TYPE 302
SAME AS TYPE 301
EXCEPT AS SHOWN




TYPE 303
SAME AS TYPE 301
EXCEPT AS SHOWN



DETAIL Y
SCALE 20:1



TYPE 301



SEALING RIBS MAY DIFFER AS SHOWN

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - PARTS ARE TO BE PACKAGED IN SEALED PLASTIC BAGS. GROSS
WEIGHT INCLUDING CARTON IS NOT TO EXCEED 34 POUNDS.
 - TO IMPROVE SEAL TO LEAD PROCESSING ON SLIPPERY OR SMOOTH CABLE
INSULATION, THE APPLICATION ENGINEER MAY SPECIFY THE NEXT
SMALLER SEAL SIZE P/N IN PLACE OF THE INDICATED SEAL FOR
THE "CABLE O.D." LISTED IN THE CHART.
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR
BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
 - SEE 12010295 SHEET 6 FOR MYLAR ASSEMBLY INFORMATION.

PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	CABLE O.D.	±0.05	SEE NOTE #3	C	EQUIVALENT CABLE SEAL	VOLUME	REPLACED BY
15397197	01	AC	-	SILICONE METHYL/VINYL BLACK	301	4.5-3.61	6	-	-	-	0.305	-
15324997	01	AD	-	SILICONE METHYL/VINYL TAN	301	2.15-1.65	6	12077759	-	-	0.363	-
15324996	01	AD	-	SILICONE METHYL/VINYL BLUE	301	4.5-3.61	6	12052668	-	-	0.305	-
15324995	01	AD	-	SILICONE METHYL/VINYL RED DK	301	2.85-2.01	6	12052388	-	-	0.357	-
15324994	01	AD	-	SILICONE METHYL/VINYL GRAY	301	3.75-2.81	6	12052387	-	-	0.335	-
15324993	01	AD	-	SILICONE METHYL/VINYL GREEN	301	5.15-4.4	6.5	12052386	-	-	0.293	-
12077759	B4	-	-	SILICONE METHYL/VINYL TAN	301	2.15-1.65	6	15324997	-	-	0.363	-
12052668	02	AD	OBsolete	SILICONE METHYL/VINYL BLUE	301	4.5-3.61	6	15324996	-	-	0.305	15324996
12052388	A4	-	-	SILICONE METHYL/VINYL RED DK	301	2.85-2.01	6	15324995	-	-	0.357	-
12052387	03	AD	OBsolete	SILICONE METHYL/VINYL GRAY	301	3.75-2.81	6	15324994	-	-	0.335	15324994
12052386	A4	-	-	SILICONE METHYL/VINYL GREEN	301	5.15-4.4	6.5	15324993	-	-	0.293	-
12045772	A2	-	OBsolete	SILICONE METHYL/VINYL GREEN	302	4.21-3.5	4.25	-	-	-	0.275	-
CABLE SEAL												

DRAWING NUMBER									
12010295									
SIZE	SCALE	FRAME NO	SHEET NO	TOTL SHEETS	REV	TRF	TRF	TRF	TRF
A1x3	10:1	1	2 OF 2	3 OF 3	R	10	-	-	-

DIMENSIONS ENCLOSED IN () INDICATE DIMENSIONS TO BE USED FOR TOOL BUILD. DIMENSIONS NOT ENCLOSED IN () ARE FOR INFORMATION ONLY.									
FROM	> 0	> 0	> 0	> 0	> 0	> 0	> 0	> 0	> 0
TO	0	0	0	0	0	0	0	0	0
REFERENCE	15324993	15324993	15324993	15324993	15324993	15324993	15324993	15324993	15324993

THIRD ANGLE PROJECTION									
DO NOT SCALE	DO NOT SCALE	DO NOT SCALE	DO NOT SCALE	DO NOT SCALE	DO NOT SCALE	DO NOT SCALE	DO NOT SCALE	DO NOT SCALE	DO NOT SCALE
USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA

DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARR, OH									
DATE	13JAN99								
DR	J. H. HUBELMAN								
APPROV	T. L. MURPHY								
APPROV	A. L. HERMANN								
APPROV	J. L. JAMES								
SUBSISTANCES OF CONCERN ARE RECORDED CONTINUED FROM DELPHI 12010295									
DRAWING TITLE TAXI SEAL CBL IW M/P									
DRAWING NUMBER 12010295									
SIZE	SCALE	FRAME NO	SHEET NO	TOTL SHEETS	REV	TRF	TRF	TRF	TRF
A1x3	10:1	1	2 OF 2	3 OF 3	R	10	-	-	-

12010295