




SECTION A-A




NOTE:

- 1- APTIV PRODUCT SPECIFICATION: FE PS 16 010
- 2- INTERFACE DRAWING: 35099339
- 3- USER'S MANUAL: PU233
- 4- FOR TORX 30 SCREW DRIVER
SCREWING TORQUE 8N.m±10%

COMPONENTS TABLE


N°	DESIGNATION	APTIV PN	QUANTITY
	FEMALE CONNECTOR	35098437	
1	OUTER PLUG	35096611	1
2	UNIT SEAL	35082112	1
3	PLASTIC CAP	35096049	1
4	SPA	35082103	1
5	SCREW M6x20 (ISO 14583)	35158044	1
6	METALLIC INSERT	33508801	1

SECTION B-B



ASSOCIATED PARTS


N°	DESIGNATION	APTIV PN	QUANTITY
7	RCS800 FEMALE TERMINAL	13893887	1
8	RETAINER	13893889	1
9	SWS	35mm ² 13893888	50mm ² 13923559




SCALE 2:1

ASSOCIATED PARTS

N°	DESIGNATION	APTIV PN	DRAWING	QUANTITY
10	HEADER	35098440	35098443	1
11	INTERFACE	-	35099339	1
12	M5 SCREW	-	-	1
13	M4 SCREW	-	-	1


FREE SPACE AREA NEEDED TO MATE AND UNMATE
THE FEMALE CONNECTOR ON THE BOX
FOR INFORMATION

SCALE 1:2



SCALE 1:1

EQUIPPED FEMALE CONNECTOR



SCALE 2:1

A LINE DRAWN THROUGH A PART NUMBER
INDICATES THAT PHYSICAL PARTS ARE NOT
AVAILABLE FOR ORDERING.PART NUMBERS THAT DO NOT HAVE A LINE PRESENT
INDICATE THAT PHYSICAL PARTS ARE AVAILABLE
FOR ORDERING.CONTACT APTIV SALES TO ASSURE
AVAILABILITY OF PARTS.LA LIGNE TRACÉE SUR LA RÉFÉRENCE
PIÈCE INDIQUE QUE LA PIÈCE N'EST PAS
DISPONIBLE À LA COMMANDE.LES RÉFÉRENCES PIÈCES QUI NE SONT PAS BARRÉES
INDIQUENT QUE CELLES-CI SONT DISPONIBLES
PHYSIQUEMENT POUR ÊTRE COMMANDEES.CONTACTER LE SERVICE COMMERCIAL DE APTIV
POUR S'ASSURER DE LA DISPONIBILITÉ DES PIÈCES.

R 0.2 MAX

R 0.1 MAX

SHARP CORNER TOLERANCE

		SHARP CORNER TOLERANCE										
DIM TO CHECK COTES A VERIFIER	DIMENSIONAL RANGE (MM)										CHART E	
	FROM TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400		
() DIM FOR HELP COTES POUR INFO	TOLERANCE UNLESS OTHERWISE SPECIFIED											
☐ THEORETIC DIM COTES THEORIQUES		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
ANGULAR TOLERANCE 2°												