



NOTA NOTE	SPECIFICATIONS
1	CONNECTEUR DOIT ETRE CONFORME AU CDC: FEMALE CONNECTOR ACCORDING TO PSA SPECIFICATION: 96 238 404 99
2	CONNECTEUR SUIVANT: FEMALE CONNECTOR ACCORDING TO: -CLASSE DE TEMPERATURE T3 SELON B217050 REV A TEMPERATURE CLASS T3 ACCORDING TO B217050 REV A -CLASSE DE VIBRATION MOTEUR SELON B217050 REV A ENGINE VIBRATOR CLASS ACCORDING TO B217050 REV A -CLASSE ETANCHEITE 2 SELON B217050 REV A SEALING CLASS 2 ACCORDING TO B217050 REV A
3	PRECONISATION D'UTILISATION: USER'S MANUAL : PU 071
4	ALVEOLE SUIVANT : CAVITY ACCORDING TO STE: 96 288 230 99
5	CONNECTEUR ET POSITION ALVEOLE CONFORMES AU PLAN D'INTERFACE : FEMALE CONNECTOR AND CAVITY'S POSITION ACCORDING TO: 211FT0289 ET/AND STE 96 339 622 99
6	CONDUCTEUR SUIVANT / WIRE ACCORDING TO: STE:96 418 794 99
7	CONDITIONNEMENT SUIVANT NORME: PACKAGING ACCORDING TO STANDARD: E73 03 150G
8	DIAMETRE DE FILS / WIRE DIAMETER MINI=1.40 MAXI=2.80
9	MASSE DU PRODUIT LIVRABLE / DELIVERY CONNECTOR WEIGHT : 6g
10	CHARNIERE DE PLAQUETTE ARRIERE ABSENTE OU CASSEE ADMISE NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
11	DEFAUTS D'ASPECT SUR ZONES NON FONCTIONNELLES ADMIS VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED






ISOLANT FEMALE HOUSING	211 I 0 074	PBT 0% FV / 0% GF	NOIR / BLACK	33501294
GRILLE TPA	211 M 0 101	PBT 15% FV 15% GF	NOIR / BLACK	33501300
	211 M 1 101		MARRON / BROWN	33508042
	211 M 2 101		ROUGE / RED	33508044
	211 M 4 101		JAUNE / YELLOW	33508040
	211 M 5 101		VERT / GREEN	33508041
	211 M 6 101		BLEU / BLUE	33508039
	211 M 8 101		GRIS / GREY	33501315
	211 M 9 101		BLANC / WHITE	33508043
GROMMET MAT SEAL	211 M 109	SILICONE	VERT / GREEN	33501309
JOINT INTERFACIAL INTERFACIAL SEAL	211 M 076	SILICONE	BLEU / BLUE	33501305
DESIGNATION	REF. FC1	MATIERE MATERIAL	COULEUR COLOUR	APN 02

								VUE F F VIEW
5.55	3.95	0.85 ⁺⁰ -0.05	0.15	2.05	3.65	1.75	0.85 ⁺⁰ -0.05	TOLERANCES : ± 0.05 ECHELLE / SCALE 3:2
NOIR / BLACK	MARRON / BROWN	ROUGE / RED	JAUNE / YELLOW	VERT / GREEN	BLEU / BLUE	GRIS / GREY	BLANC / WHITE	COULEUR / COLOUR
211 PC 03 25 0 349	211 PC 03 25 1 349	211 PC 03 25 2 349	211 PC 03 25 4 349	211 PC 03 25 5 349	211 PC 03 25 6 349	211 PC 03 25 8 349	211 PC 03 25 9 349	REF.FC1
10865146	33501994	10889570	33501995	10889574	10889569	10890168	10889568	APN 02





JOINT INTERFACIAL : VUE EN COUPE
INTERFACIAL SEAL : SECTION VIEW





VUE F
F VIEW

COUPE A-A / SECTION A-A



3				2				1			
DWG STATUS				REVISION HISTORY				AUTH			
DATE	STG	REV	N/P/CHG	ZONE							
08DE17	-	01			FILE TRANSLATED FROM MVL SYSTEM REBRAIN IN NX				V.K	SCH	SCH
250C24	R	02	--	-	B10, A5 APN ADDED				AR	SCH	TT



ECHELLE / SCALE 1:1

CODAGE NOIR REPRESENTE
BLACK CODING DRAWN

DWG TYP PART DRAWING	DISTR CODE D
WEIGHT (GR)	
VOLUME (CM³)	
ROUTING	
UNLESS OTHERWISE SPECIFIED	
GENERAL TOLERANCES ACCORDING TO: ± 0.1 ± 2°	
GD&T ACCORDING TO:	
REFERENCE 211 FT 0479	
FIRST ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	

• APTIV •	
CONNECTION SYSTEMS Chennai, India	
COPYRIGHT 2024 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DIESE ZEICHNUNG IST EIGENTUM DER FIRMA DELPHI UND ENTHAELT DELPHI VERTRAULICHE INFORMATIONEN. DIE REPRODUKTION, VERTEILUNG UND NUTZUNG DIESER DOKUMENTES ODER DEREN ZUGEHÖRIGEN CAD DATEN, ODER AUCH ALS KOMMUNIKATION VON BELIEBIGEN INHALT ZU ANDEREN, IST OHNE BERECHTIGUNGSPRUEFUNG DURCH DIE DELPHI CORPORATION UNZULAESSIG	
DR	SCHMITT
APVD1	KAREEM
APVD2	TECZA
APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 POTENTIELL GEFÄHRLICHE STOFFE UND REZYKLATANTEIL GEMÄSS DELPHI 10949001	
MATERIAL -	
DRAWING NAME MINI SEALED NM FEMALE CONNECTOR 3-WAY 1.5 FEMALE HOUSING	
DRAWING NUMBER 10858478	
SIZE A1	SCALE 3:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 02
N/P --	