







PART NO
1216 0939



SAME AS TYPE 101
EXCEPT AS SHOWN

[illegible]

TYPE 101




NOTES — 1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
CAVITIES ARE IDENTICAL
LOCKING FEATURES ARE IDENTICAL

3. MATING COMPONENTS:
TERMINAL 12040502 OR EQUIVALENT

4. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.

12160938	A		PM002043 001 PP 40% TF - GRAY	12135124	102
12015308	B		RO067557 PP 40% TF - BLACK	12088547	101
PART NO	REV	STATUS	MATERIAL SPEC & COLOR	MATING CONN	TYPE

Ugraphics II		METRIC DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED	
THIRD ANGLE PROJECTION		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR $\pm 2^\circ$	
		ONE PLACE ± 0.3 TWO PLACE ± 0.15	
CODE NO	QC	DES	
6900			
DWG DATE	24AU94	DR SERGIO MORAN	24AU94
SCALE	2:1	CK SERGIO MORAN	24AU94
REFERENCE NO	12160939	APPR CUMMINGS	09SE94
SIZE	"R5"	VOL CM ³	15.932
MATERIAL SPEC			
SEE CHART			
NAME			
TAXI CONN 8 WAY PC EDGBD-STD			
PART NUMBER			
1216		0939	
PRODUCT INFORMATION DWG		SIZE A1	