





ID-NR. / PART-NO.:	PART-REV	DATE DATUM	MATERIAL WERKSTOFF	RAL
415 784 / 12131237	01	10FE84	PA6 BLK	---


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
12JL83		00				CREATION OF ORIGINAL DESIGN (TRANSPARENCY) ERSTELLUNG DER ORIGINALZEICHNUNG (TRANSPARENT)		WTR.	JOR.	
10FE84		01			A6 B8	MATERIAL NAME AND TOOL CAVITY NUMBER ADDED WERKSTOFF UND NESTKENNZEICHEN HINZU		LUCKE	JOR.	
140C97	R	01	AA			DRAWING ON CAD NEW DRAW UP ZEICHNUNG AUF CAD NEU ERSTELLT		U/GAT	SEUT	R.WIS



TOOL CAVITY NUMBER  
NESTKENNZEICHNUNG  
①

MATERIAL NAME  
FORMAT ACCORDING TO DIN 1451; H=1MM; 0.2 MM RAISED  
WERKSTOFFKENNZEICHNUNG  
SCHRIFTART NACH DIN 1451; H=1MM; 0.2 MM ERHABEN  
①

SCALE / MASSSTAB:  
**1:1**



DWG TYP <b>PART DRAWING</b>	
WEIGHT (GR)	DISTR CODE
VOLUME (CM³)	D
ROUTING	

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES  
ACCORDING TO:  
SEE CHART  
SIEHE TABELLE

GD&T  
ACCORDING TO:  
ISO 1101

ORIGINAL DESIGN  
6301.063 K

REFERENCE  
**PART DRAWING**

FIRST ANGLE PROJECTION

DO NOT SCALE  
USE MATH DATA

# DELPHI

DELPHI DEUTSCHLAND GMBH  
D-42119 WUPPERTAL

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION.  
NO RIGHTS ARE GRANTED TO USE THIS DRAWING FOR ANY PURPOSE OTHER  
THAN THE FURNISHING OF SERVICES AND SUPPLIES TO DELPHI  
CORPORATION.

DIESE ZEICHNUNG IST EIGENTUM VON DELPHI CORPORATION  
ES IST NICHT GESTATTET, DIESE ZEICHNUNG FUER ANDERE  
ZWECKE ALS FUER DIE BEREITSTELLUNG VON DIENSTLEISTUNGEN UND WAREN  
AN DELPHI CORPORATION ZU NUTZEN.

DR	DATE
U/GAT	130C97
APVD1 SEUT.	130C97
APVD2 R.WISNIEWSKI	140C97
APVD3	
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001  
POTENTIELL GEFÄHRLICHE STOFFE UND REZYKLATANTEIL  
GEMÄSS DELPHI 10949001

MATERIAL  
**SEE CHART / SIEHE TABELLE**

DRAWING NAME  
**RECEPTACLE HOUSING 1 WAY  
FOR FEMALE TERMINAL 4.8**

**FLACHSTECKHUELSENGEHAEUSE 1 POL.  
FUER HUELSE 4.8**


DRAWING NUMBER  
**13677077**

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A2	5:1	1 OF 1	1 OF 1	R	01	AA

ARCHIVES : 030E07

KEY PRODUCT CHARACTERISTICS				
	SAFETY/COMPLIANCE		FIT/FUNCTION	TOTAL ON DRAWING <b>0</b>
	S/C CHECKPOINTS		F/F CHECKPOINTS	LAST NO. USED <b>0</b>
NO & TYPE	DESCRIPTION	RATIONALE	PTS	ZONE
-	-	-	-	-

DIN TO CHECK PRUEFMASSE	DIMENSIONAL RANGE (MM)										CHART E1
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	
1	TO	20	30	70	100	150	200	250	300	400	
	TOLERANCE UNLESS OTHERWISE SPECIFIED										
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
	ANGULAR TOLERANCE ±2°										



CONTROLLED DOCUMENTS ARE ONLY AVAILABLE ON THE SERVER