









TYPE 101




SECTION A-A




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



MATERIAL RECYCLING
CODE OPTIONAL



(1) X (0.1) RAISED
CHARACTERS AS SHOWN.



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469, (1.06)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGES, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- (1.5)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
- PART(S) RESTRICTED ARE NOT INTENDED TO BE USED AS "STAND ALONE" TEST CONNECTORS, AND SUCH DO NOT CONFORM TO SAE J-1962. THESE CONNECTORS ARE DESIGNED TO BE USED AS PART OF AN INSERT MOLDED MALE OBD-II TEST CONNECTOR ASSEMBLY (REFERENCE DELPHI P/N 121102561). THE MOLDED ASSEMBLY INCLUDES A CONNECTOR LOCK AND AN OVER-MOLD TO ALIGN AND STABILIZE THE MALE BLADES. REFER TO CHART FOR SPECIFIC RESTRICTED PART NUMBERS.
- FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

DRAWING NUMBER 13532294									
SIZE A1x3	SCALE 5:1	FRAME NO 2	SHEET NO 2	SHEET OF 11	REV 04				

13532292	02	AB	-	RESTRICTED-SEE NOTE 6	102	POLYESTER COMPOUND BLUE	8.402
12110252	F7	-	-	RESTRICTED-SEE NOTE 6	101	POLYESTER COMPOUND RED	8.542
PART NO	REV	N/P	STATUS	RESTRICTED USAGE	TYPE	MATERIAL SPECIFICATION AND COLOR	VOLUME CM³
15							

DIMENSIONAL RANGE (MM)									
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
TO	20	30	70	100	150	200	250	300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED									
FRACTIONAL TOLERANCE									
DECIMAL TOLERANCE									
ANGULAR TOLERANCE									

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE

KOREN, OH

DATE	09.JUN05
DR	R. TOVAR VALDEZ
APPROV	J. VILLAMIL
APPROV	JUAN GONZALEZ
APPROV	
APPROV	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (104500)	
DRAWING NAME	
TAXI CONN M M/P 150	
DRAWING NUMBER	
13532294	
SIZE	A1x3
SCALE	5:1
FRAME NO	1
SHEET NO	2
SHEET OF	11
REV	04
N/P	

DATE

09.JUN05

DR

R. TOVAR VALDEZ

APPROV

J. VILLAMIL

APPROV

JUAN GONZALEZ

APPROV

APPROV

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (104500)

DRAWING NAME

TAXI CONN M M/P 150

DRAWING NUMBER

13532294

SIZE

A1x3

SCALE

5:1

FRAME NO

1

SHEET NO

2

SHEET OF

11

REV

04

N/P

40SS3231