












TYPE 101



SECTION A-A

SYMBOL DEFINITION				MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.				NO MISSING SYMBOL NUMBER	
				LAST NO. USED	
				10	



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
- FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
- INADVERTANT ENGAGE FORCE OF THE PLR FROM PRE-STAGE TO THE LOCKED POSITION CAN BE BETWEEN 13 AND 21 N. (GMW 3191 SPEC IS > 20 N).
- FORCE REQUIRED TO LOCK THE CPA FROM PRE-STAGED POSITION CAN BE BETWEEN 36 AND 43 N. (GMW 3191 SPEC IS < 22 N).
- FORCE TO REMOVE THE CPA FROM THE CONNECTOR CAN BE BETWEEN 42 AND 63 N. (GMW 3191 SPEC IS > 60 N).
- CONNECTOR - CONNECTOR ENGAGE FORCE CAN BE MAX. OF 50N.

13915046	01	AB	103	13915037	13739318	13738749	13738759	13738761	13738745
13915044	01	AB	102	13915036	13739318	13738749	13738759	13738761	13738745
13915043	01	AB	101	13915030	13739318	13738749	13738759	13738761	13738745
13766241	02	AA	103	13766240	13739318	13738749	13738759	13738761	13738745
13738744	03	AA	102	13738741	13739318	13738749	13738759	13738761	13738745
13738743	03	AA	101	13738740	13739318	13738749	13738759	13738761	13738745
PART	NO	REV	N/P	CONNECTOR	CPA	CABLE SEAL	STRAIN RELIEF	PLR	CONNECTOR SEAL

DIMENSIONAL RANGE (MM)			
FROM	> 0	> 20	> 30
TO	20	30	70
TOLERANCE (mm)			
	±0.15	±0.2	±0.3
ANGLES			