






①②③④⑤⑥ TWP08M



- 주 기 -

- 1. 사용상 유해한 흠, BURR등이 없을 것.
- 2. 명시되지 않은 공차는 일반공차에 준할 것.
- 3. CAV. No. 및 MARKING은 당사규격에 준하여 각인할 것.
- 4. ASSY 부품

1) FRONT HOLDER:33147584/HP291-08100

2) TERMINAL

적용 전선(SQ)	KUM PART NAME	KUM P/No.	APTIV P/No.
AESSXF 0.22	TWP-M-SS	TP101-00400	35296476
AESSXF 0.3-0.5	TWP-M-S	TP101-00100	33151931
AESSXF 0.22	TWP-M-SS-Au	TP101-00410	35296477
AESSXF 0.3-0.5	TWP-M-S-Au	TP101-00110	35296475
AESSXF 0.22	TWPII-M-SS	TP231-00400	35296435
AESSXF 0.3-0.5	TWPII-M-S	TP231-00200	35277194
AESSXF 0.22	TWPII-M-SS-Au	TP231-00410	35296436
AESSXF 0.3-0.5	TWPII-M-S-Au	TP231-00210	35296434



3) WIRE SEAL

적용 전선 표준사양경	KUM PART NAME	KUM P/No.	APTIV P/No.
Φ0.9	W/S TWP-0.9S(MB)	EU020-01140	35187200
Φ1.4	W/S TWP-1.4S(BR)	EU020-01050	15517491
Φ1.6	W/S TWP-1.6S(GN)	EU020-00030	15523552
-	W/S TWP-V(R)	EU020-00060	15517565


6. 본 부품은 방수형 CONNECTOR 임.

7. APTIV Drawing No : 35296499




⑦ F/H TWP08M



ISO VIEW



SECTION A-A



GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	150MAX	200MAX	200VR	ANGLE
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4	±30'

⑦	F/H TWP08M-OR	HP291-08100	33147584	ORANGE	PBT
⑥	TWP08M-GY	HP281-08120	35339503	GRAY	PBT
⑤	TWP08M-BR	HP281-08050	35296497	BROWN	PBT
④	TWP08M-L	HP281-08040	35296496	BLUE	PBT
③	TWP08M-GN	HP281-08030	35296495	GREEN	PBT
②	TWP08M-W	HP281-08010	35339500	WHITE	PBT
①	TWP08M-B	HP281-08020	33151928	BLACK	PBT
NO.	KUM PART NAME	KUM P/No.	APTIV P/No.	COLOR	MATERIAL
	THIRD ANGLE PROJECTION	A	2/1	KOT	CWJ
		TOLERANCE	SCALE	DESIGN	DRAWN
				CHECKED	APPROVED

	19.08.19	-	1	ADDED APTIV P/No.	KKJ
CJW	15.08.13	E015-0254	B	단자 사양 추가(4개소)	CWJ
CJW	12.07.04	E012-0078	A	색상 추가(5개소)	KHR
CJW	09.06.26	E009-0126	-	신 규	LWY
승인	DATE	NOTE No.	SYM	ALTERATION	담당
DRAWING NAME TWP08M-B					
DRAWING No. HP281-08020-C01					
● APTIV ●					