













SCALE 3:1



NOTE:

1. HOUSING RAW MATERIAL: PBT 15 GLASS FIBER
HOUSING TENSILE MODULUS: 5600 MPa at 20° C
2. CONTACTS RAW MATERIAL; CuZn37; TIN OR GOLD PLATING
3. PRODUCT ACCORDING TO PSA SPECIFICATION: 9604596299
4. KEY CODE GREY-BROWN NOT SHOWN



DWG. TYPE	PART DRAWING
WEIGHT (G)	
VOLUME (CM³)	
ROUTING	

UNLESS OTHERWISE SPECIFIED	
GENERAL TOLERANCES	
ACCORDING TO:	
± 0.1mm / ± 0.5°	
OD&T	
ACCORDING TO:	

REFERENCE	
FIRST ANGLE PROJECTION	

DO NOT SCALE	
USE MATH DATA	

DIM TO CHECK	
() DIM FOR HELP	
THEORETIC DIM	

R 0.1 MAX	
R 0.2 MAX	
SHARP CORNER TOLERANCE	

•APTIV•	
CONNECTION SYSTEMS	
Chennai, India	
COPYRIGHT 2025 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	29AP25
DR	A.M.B RIFAN
APVD1	N.ARUN
APVD2	S.RAMACHANDRAN
APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV (094900)	
SEE NOTE	
DRAWING NUMBER	
24 WAY RECEPTACLE 90°	
33501644	
SIZE	A0
SCALE	3:1
FRAME NO	1 OF 1
SHEET NO	1 OF 2
STG	R 02
REV	
NVP	

