





FORMED PART

PART NO:	PART-REV	DATE / DATUM	MATERIAL WERKSTOFF	M-SPEC	SURFACE OBERFLAECH	STRENGTH FESTIGKEIT N/MM²
35508557	01	03NO20	X10CrNi18-8	M8212L13	PRE-PLATED UNDERPLATE: Ni 1.25-2.5µm TOP PLATE : Sn 2.5-6µm	-


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
03NO20	R	01				INITIAL RELEASE		S.M	V.VOL	G.DRO




FERRULE ON REEL



BLANK PART



MASSSTAB / SCALE 2:1



• APTIV •

CONNECTION SYSTEMS
Chennai, India
COPYRIGHT 2020 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.
DIESE ZEICHNUNG IST EIGENTUM DER FIRMA APTIV UND ENTHAELT APTIV VERTRAULICHE INFORMATIONEN. DIE REPRODUKTION, VERTEILUNG UND NUTZUNG DIESER DOKUMENTES ODER DEREN ZUGEHÖRIGEN CAD DATEN, ODER AUCH ALS KOMMUNIKATION VON BELIEBIGEN INHALT ZU ANDEREN, IST OHNE BERECHTIGUNGSPRUEFUNG DURCH DIE APTIV UNZULAESSIG.
DR S.MANOCHARAN
APVD1 V.VOLKOV
APVD2 GERT DROESBEKE
APVD3
APVD4
APVD5
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
POTENTIELL GEFAEHRLICHE STOFFE UND REZYKLATANTEIL
GEMAESS APTIV 10949001

SEE CHART / SEE TABELLE



OUTER CRIMP FERRULE

DRAWING NUMBER
35508558

SIZE A1 SCALE 10:1 FRAME NO 1 OF 1 SHEET NO 1 OF 1 STG REV N/P R 01 -

DESIGNATED CHARACTERISTICS					QC I	KPC	
0		LAST NO USED		K OR Q IN SYMBOL INDICATES CHECKPOINT	FIT/FUNCTION	 CI	 FF
0	0	TOTAL ON DRAWING					
KPC	QC I	SAFETY/COMPLIANCE				 SC	
NO	NO	TYPE	DESCRIPTION	RATIONALE			
						ZONE	SH
							PTS

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
MIT EINER LINE DURCHGESTRICHENE PART-NR. GEKENNZEICHNET, DASS DIESE PART-NR. NICHT BESTELLT WERDEN KANN.	
PART-NR. DIE KEINE LINE ZEIGEN, KENNZEICHNEN, DAS TEILE ZUR BESTELLUNG VERFUEGBAR SIND.	
FUEHR VERFUEGBARKEIT DER PARTS DEN EINKAUF VON APTIV KONTAKTIEREN.	
SHARP CORNER TOLERANCE	
DIMENSIONAL RANGE (MM)	
FROM 0	CHART D
TO 12	> 12
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE ±2°	

DWG. TYP PART DRAWING	
WEIGHT (GR)	DISTR CODE D
VOLUME (CM³)	
ROUTING	
UNLESS OTHERWISE SPECIFIED	
GENERAL TOLERANCES ACCORDING TO: SEE CHART SIEHE TABELLE	
GD&T ACCORDING TO: ISO 1101	
REFERENCE	
FIRST ANGLE PROJECTION 	
DO NOT SCALE 	
USE MATH DATA 	