

One For All



C10 Duo

100W Dual USB-C Power Adapter

100W

Output Max

GaN

Technology

**PD 3.0 (PPS)
QC 4.0**

Fast Charge

75% PCR

Recycled
Material Case



Reversible
Dual Port



Innergie 3 Fast Charge Modes

Any Single Port




100W

Dual Port



65W + 30W



45W + 45W



150+
Countries
Travel Convenience

114 c.c.

37% smaller than
original
power adapter



FSC

Plastic Free
Packaging

**Concise
Gapless**



100%

Renewable
Electricity

**Foldable
Plug**



DOE VI

High Efficiency
Standard

Macbook Pro M2

50%

30 mins

iPhone 15

50%

25 mins



InnerShield™



GreenSense™



Warranty

Product Spec

Input	USB-C Output	Dimensions and Weight	Fast Charge Protocol	Compatibility
100-240V AC / 1.7A 50-60Hz	5V / 3A ; 9V / 3A 12V / 3A ; 15V / 3A 20V / 5.0A PPS 5V-21V / 3A	56 x 67 x 30.4 mm 230 g	PD 3.0 (PPS) QC 4.0 SFC 25W Apple Mode DCP	Compatible with most USB-C (Type-C) devices, MacBook, iPad, Chromebook, etc.

3 Years Warranty

- * 3-Year Warranty and Replacement Service for Innergie Members.
- * Please present the purchase proof (physical or electronic invoice) for the purchase date
- * Please note that if there is no purchase date, the warranty start date will be the warehouse release date plus 3 months.