Long Travel J SMT
Washable Type

Water-proof Dust-proof Halogen Free RoHS Compliant

FEATURES

※Sharp click feeling with soft sound
※Long travel
※Sealed IP67

APPLICATION

※Automotive
※Instrument
※Industrial

SPECIFICATION

Contact Rating	10uA, 1V DC min. 50mA, 16V DC max.
Contact Resistance	100mΩ max.(initial)
Insulation Resistance	100MΩ min.
Dielectric Strength	250V AC/1 minute
Operating Force	350±90gf
Operating Life	100,000 cycles min.
Operating Temp.	-40°C ~ +85°C
Storage Temp.	-55°C ~ +85°C

HOW TO ORDER

T 6 V J □ □ G Q R

- J Bend
- Total Height: 1=4.9mm
- Operating Force: 1=350gf
- Plating: G=Silver Plating
- Halogen Free
- Package: Tape & Reel

CIRCUIT



PACKAGE

<Tape & Reel>
1000 pcs

T6VJ









P.C.B. LAYOUT