





LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-19-015552	11NOV2019	KD	FL
			B1	ECR-21-121338	24NOV2021	KD	FL
			C	ECR-21-123888	16DEC2021	DC	FL
			C1	ECR-22-126910	24JAN2022	DC	FL



P/N 0-293153-3 AS SHOWN
SCALE 5:1 / 10:1

- 1 WIRE RANGE : STRANDED 0.22-0.35 mm² (INS. DIA. 1.30±0.1)
- 2 MATING PART: PCB FRAME P/N 964575 (PCB THK 1.5±0.14 COPPER CLADDING INCLUDED) SEE PRODUCT SPEC. 108-18056 FOR FRAME APPLICATION
- 3 KEYING RIBS TO BE REMOVED BY TERMINATION MACHINE
- 4 CUT OFF DIMENSION DUE TO PRODUCTION PROCESS
- 5 CIRCUIT No. IDENTIFICATION
- 6 TE TRADEMARK (OPTIONAL POSITION)
- 7 TAMPOGRAPHIC COLOUR CODE AREA (P/Ns IDENTIFICATION BEFORE CRIMPING)
- 8 POLARIZATION RIB BETWEEN CAVITIES. (SEE BELOW TYPICAL POLARIZATION CUTOFF ON PCB)
- 9 PRELIMINARY PART NOT RELEASED FOR PRODUCTION.
- 10 PBT GF
- 11 PBT GF, GWEPT 750 NO-FLAME, NATURAL
- 12 ALTERNATIVE RESIN PBT GF
- 13 PART RELEASED WITH PARTIAL VALIDATION AND PENDING AGENCY APPROVAL
- 14 (REPLACES NOTE 11) PA GF, UL94-V0 & GWEPT 750 °C NO FLAME, NATURAL



	GREEN	SELECTIVELY 1.3.5.7.9	1/2	9	20.0	24.9	/	7-2311505-9	/
	-	SELECTIVELY 1.4.7.8.9	2/3	9	20.0	24.9	2-293153-9	/	2-2403117-9
	BLUE	SELECTIVELY 1.2.4.5.6.7.8.9	2/3	9	20.0	24.9	1-293153-9	6-2311505-9	1-2403117-9
	BLACK	SELECTIVELY 1.3.4.6.8.9					0-293153-9	5-2311505-9	2403117-9
	RED	SELECTIVELY 1.2.3.7.8	1/2	8	17.5	22.4	0-293153-8	2-2311505-8	2403117-8
	BLACK	SELECTIVELY 1.3.5.6.7	2/3	7	15.0	19.9	1-293153-7	/	1-2403117-7
	BLACK	SELECTIVELY 1.4.5.6.7	2/3	7	15.0	19.9	0-293153-7	6-2311505-7	2403117-7
	BLACK	SELECTIVELY 1.3.4.6	1/2	6	12.5	17.4	2-293153-6	6-2311505-6	2-2403117-6
	RED	SELECTIVELY 1.3.4.6	2/3	6	12.5	17.4	1-293153-6	5-2311505-6	1-2403117-6
	BLACK	SELECTIVELY 1.2	1/2	6	12.5	17.4	0-293153-6	4-2311505-6	2403117-6
	BLACK	SELECTIVELY 3.4	3/4	4	7.5	12.4	0-293153-4	2311505-4	2403117-4
	BLACK	SELECTIVELY 1.3	1/2	3	5.0	9.9	0-293153-3	8-2311505-3	2403117-3
NOTES:	COLOUR CODE	CONTACT LOADING	POLARIZ. RIB POS.	HSG POS.	M.A	DIM.B	TE P/N	TE P/N	TE P/N

-	-	-	-	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.CORDALO CHK G.TURCO APVD G.TURCO	28NOV2005 28NOV2005 28NOV2005	 TE Connectivity	
SEE TABLE	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT	2	DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P.LC ± 0.2 1 P.LC ± 0.2 2 P.LC ± 0.2 3 P.LC ± - 4 P.LC ± - ANGLES FINISH ±°	NAME	DUOPLUG 2.5 FEMALE CONNECTOR STANDARD VERSION, KEYPED (SELECTIVELY LOADED)	
	PBT GLASS FIBER FILLED	FEMALE HOUSING	1						
Q.TY	MATERIAL	DESCRIPTION	ITEM			PRODUCT SPEC 108-18056		SIZE	RESTRICTED TO
1	REVISIONE DELL'ASSEMBLATO (REVISION OF EACH ASSY NOI)			MATERIAL SEE TABLE		APPLICATION SPEC 114-18049-1		CAGE CODE A1 00779	DRAWING NO C=293153
Q.1A* PER ASSEMBLATO (QTY REQ'D PER ASSY)	ELENCO DEI COMPONENTI (PARTS LIST)			-		WEIGHT -		SCALE 10:1	SHEET 1 OF 1
						CUSTOMER DRAWING		REV C	