

SPECIFICATIONS		REV.	BY	DATE	PART NO.
RESISTANCE RANGE	100 TO 100K OHMS	A	BT	1-16-93	DW22
RESISTANCE TOLERANCE	±5%				
ACCURACY	±0.35% OF VOLTAGE RATIO				ADDED SPECIFICATIONS
REPEATABILITY	±0.02% OR RESOLUTION OF POT				
RESOLUTION	SEE POT SPECIFICATIONS	B	AT	2-20-02	ADDED 1 TURN POTENTIOMETER
POWER RATING	2 WATTS				
OPERATING TEMPERATURE	-30°C TO +85°C				
TEMPERATURE COEFFICIENT	±20 PPM/°C				
TURNS	10 (000 TO 999 COUNTS)				
TERMINALS	GOLD PLATED LUGS				



HOUSING MATERIAL ----- HIGH TEMP. BLACK PLASTIC

NOTES:

1. USE ETI SYSTEMS POTENTIOMETERS MODEL MW22B.
2. POTENTIOMETERS MAY BE 1,3,5,10 TURNS.
ALSO MULTIPLE GANGS.
3. DIAL AVAILABLE WITHOUT POT, ASK FOR DA10N
4. THREADS WILL ACCEPT PANEL THICKNESS OF 3/16 MAX.
5. SEE POTENTIOMETER CATALOG FOR ADDITIONAL SPECIFICATIONS.

*MODEL WITH MW20B IS DW20.

SCHEMATIC



	THIS DOCUMENT CONTAINS PROPRIETARY DATA OF POLARIS INDUSTRIAL ENTERPRISES, INC. NO DISCLOSURE, REPRODUCTION, OR USE OF ANY PART THERE OF MAY BE MADE EXCEPT BY WRITTEN PERMISSION.		ETI CARLSBAD SYSTEMS CALIFORNIA PART NO. DW22	
	SCALE	NONE	TITLE POT/DIAL COMBINATION	
	DATE:	5-8-87		
	BY			
TOLERANCES XX = +/- .010" FRACT. = +/- 1/64" XXX= +/- .005" ANGLES = +/- 1/2° ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.	APPR'VD	BT		
	CODE IDENT: 19477			