



Dimensions: mm.

SPECIFICATIONS	
Body:	Phenolic resin
Color:	Black
Indicator type:	Painted, an S.Q. point
Indicator color:	White
Shaft hole:	$\phi .25$
RoHS Compliant by Exemption	

MOUSER STOCK NO.	A	B	C	D	E	Screw Type
450-2034-GRX	12.3	9.5	15.5	14.2	1.6	M3x0.5
450-2035-GRX	15.7	12.0	20.3	15.6	2.0	M3x0.5
450-2036-GRX	19.5	15.0	24.0	20.0	2.2	M4x0.7
450-2039-GRX	28.6	23.3	34.8	17.8	2.8	M4x0.7