







ISSUE NUMBER	
ORIGINAL	①
UPDATE DRAWING	
Y.Z	DEC.20/2018
	②

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.

TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.35
.XX	±0.25
.XXX	±0.15



NO.	DESCRIPTION	QTY.	MATERIAL	FINISH/COLOR
4	LATCH	2	STAINLESS STEEL	TIN(MATTE)100-200 μ"
3	CONTACT	36	COPPER ALLOY	SEE NOTES
3	INSERT MOLDING	9	L.C.P GLASS REINFORCED, UL94 V-0	SEE NOTES
2	CAP	1	L.C.P GLASS REINFORCED, UL94 V-0	BLACK
1	HOUSING	1	L.C.P GLASS REINFORCED, UL94 V-0	SEE NOTES



NOTES:

MATERIAL:
HOUSING:
CAP:
INSERT MOLDING:
LATCH:
CONTACT:

L.C.P GLASS REINFORCED, UL-94V-0
L.C.P GLASS REINFORCED, UL-94V-0,
COLOR: BLACK
L.C.P GLASS REINFORCED, UL-94V-0
STAINLESS STEEL, TIN (MATTE) 100-200" μ
COPPER ALLOY
30 μ" GOLD PLATING ON CONTACT AREA
MATTE TIN PLATING ON SOLDER TAIL OVER
NICKEL UNDER PLATING

MINI SAS HD INTERNAL, VERTICAL SMT, FEMALE, 72 CONTACTS

ACAD REFERENCE NO.: 900-072-629-002

DRAWN: W.T DATE: JUNE.28 /2018

CHECKED: DATE:

SCALE: N.T.S SHEET 1 OF 1

DRAWING NUMBER: 900-072-629-002 ISSUE

PART NUMBER: 900-072-629-002 2



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR ROHS COMPLIANCY.



EDAC INC
TORONTO, ONTARIO
CANADA

YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.