










Schnitt A-A / cross section A-A
Darstellung ohne Knickschutztülle / indicated without tension relief




Zubehör / Accessories



11	Farbprägefolie <i>Colour embossing foil</i>	1	UBM300 blau 45 mm <i>UBM300 blue 45 mm</i>
10	Planschnittfolie LDPE <i>foil LDPE</i>	1	350 mm breit <i>350 mm wide</i>
9	Zugentlastungsbügel <i>strain relief clamp</i>	2	
8	Zylinderschraube M2,5x10 <i>cylinder head screw M2,5 x 10</i>	2	ISO 1207
7	Sechskantmutter M 2,5 <i>hex nut M 2,5</i>	4	ISO 4032
6	Blindstopfen <i>blind plug</i>	2	
5	Zylinderschraube M3x19,0 <i>cylinder head screw M3 x 19,0</i>	2	
4	Zylinderschraube M2,5x16 <i>cylinder head screw M2,5 x 16</i>	4	ISO 1207
3	Knickschutztülle <i>tension relief</i>	1	
2	Kabelführung <i>cable guide</i>	2	
1	Halbschale KSG 204 <i>Half shell KSG 204</i>	2	
Pos. Nr. <i>Pos. no.</i>	Benennung <i>Designation</i>	Stückzahl <i>Quantity</i>	Bemerkung <i>remark</i>

Copyright by ERNI Production GmbH & Co. KG
Proprietary notice pursuant to ISO 9001 to be observed.

Information:				Tolerances				Scale		1:1	
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation			
								204000			
a		27.09.2016		www.ERNI.com		Class		KSG204		A2	
Index		Date									