




WIRING TABLE


C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
19	AWG 30	19
20	AWG 30	20

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT(500VDC)TEST.
2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
4.)WHITE LABEL CONTENT:

DATA CODE
HARTING P/N

HARTING P/N	REVISION	Cable length (L)
3315 243 010 0177	00	100 ± 3
3315 243 020 0177	00	200 ± 3
3315 243 050 0177	00	500 ± 5

		All Dimensions in mm		Scale		Free size tol.		Ref. \					
		Original Size DIN A3		2:1		\		Sub. \					
	All rights reserved		Created by		Inspected by		Standardisation		Date		State		
	Department HCS - CN		LIT						2015-06-09		In Work		
HARTING Customised Solutions			Title									Doc-Key / ECM-Nr.	
			Har-Flex 20Pole,Dul-end,With SR,L=XXMM									100625348/UGD/000/A	
D-32339 Espelkamp			Type		Number							Rev.	Page
			TB		33 15 243 XXX0177							A	1/1