




WIRING TABLE

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
39	AWG 30	39
40	AWG 30	40

HARTING P/N	REVISION	Cable length (L)
3315 243 010 0308	00	100 ± 3
3315 243 020 0308	00	200 ± 3
3315 243 050 0308	00	500 ± 5

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT(500VDC)TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE
HARTING P/N

	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol. \\		Ref. \\	
	All rights reserved Department HCS - CN		Created by ZENGL	Inspected by	Standardisation	Date 2018-02-05	State In Work
HARTING Customised Solutions D-32339 Espelkamp		Title Har-Flex 40Pole,Dul-end,With SR,L=XXMM				Doc-Key / ECM-Nr. 100765155/UGD/000/A	
		Type TB	Number 33 15 243 XXX0308			Rev. A	Page 1/1