

Customer Information Sheet

IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm








TABLE 1: DIMENSION VARIANTS		
PART No.	DIM 'A'	DIM 'B'
G125-2249600-02-04-00	16.15	21.05
G125-2249600-03-08-00	22.40	27.30
G125-2249600-04-04-00	23.65	28.55
G125-2249600-02-24-00	28.65	33.55
G125-2249600-04-16-00	31.15	36.05
G125-2249600-06-08-00	33.65	38.55

- NOTES:
1. PACKING: BAG.
 2. HOUSING TO BE USED WITH G125-0010005 OR G125-0020005 SIGNAL CONTACTS, IN THE SIGNAL CONTACT POSITIONS, AND G125-0500005 POWER CONTACTS IN THE POWER POSITIONS.
 3. FOR SIGNAL CONTACT CRIMPING ASSEMBLY INSTRUCTIONS SEE INSTRUCTION SHEETS IS-37 & IS-38. FOR POWER CONTACT CRIMPING ASSEMBLY INSTRUCTION SEE INSTRUCTION SHEETS IS-44 & IS-47.
 4. FOR MATERIALS DETAIL AND SPECIFICATIONS SEE GECKO SERIES SPECIFICATION COMPONENT SPECIFICATION C125XX (LATEST ISSUE).
 5. G125-2249600-03-08-00 SHOWN FOR ILLUSTRATION PURPOSES ONLY, SEE ORDER CODE FOR VARIANTS.
 6. METAL BACKSHELLS ARE AVAILABLE FOR THIS RANGE.

ORDER CODE:

G125-2249600-XX-XX-00

No. OF POWER

CONTACTS: SEE TABLE 1

No. OF SIGNAL CONTACTS:

SEE TABLE 1

JD	2	19.02.25	35758
NAME	ISS.	DATE	CN/CO
APPROVED:		J.DEAN	
CHECKED:		A.YEOMANS	
DRAWN:		J.DEAN	

HARWIN

www.harwin.com

TOLERANCES
X. = $\pm 1\text{mm}$
X.X = $\pm 0.50\text{mm}$
X.XX = $\pm 0.20\text{mm}$
X.XXX = $\pm 0.01\text{mm}$
ANGLES = $\pm 5^\circ$
UNLESS STATED

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

MATERIAL & FINISH:

GLASS FILLED PA1T
UL94V-0, GREEN

TITLE:
**G125 MT SERIES
FEMALE CABLE HOUSING**

DRAWING NUMBER:
G125-2249600-XX-XX-00

SHT
2
OF
2