

Data Sheet

Microwave Cable Assemblies

SF550E/11PC24/11PC24/36in Part No.: 85157329

Main characteristics

SUCOFLEX 550E microwave cable assemblies set a new measurement standard through 50 GHz



Product configuration

Cable Type	SUCOFLEX 550E			
Lenght	914.0 mm 36.0 in REF to REF			
	Type	Series		
Connector A	SF_11_PC24-503	2.4mm	straight	plug
Connector B	SF_11_PC24-503	2.4mm	straight	plug

Technical data

Electrical data

Impedance	50.0 Ω
Operating Frequency max	50.0 GHz
Min. Return Loss	14.9 dB VSWR 1.439
Max. Insertion Loss	4.02 dB
Signal Delay	4.3 ns/m
Propagation Velocity	77.0 %
Screen Effectiveness	$\geq$ 90.0 dB 26.5 GHz
Amplitude stability vs.Flex[$\pm$]	0.1 dB
Phase Stab vs.Flexure	0.35 $^{\circ}$ /GHz

Mechanical data

Cable Diameter max	3.7 mm
Minimum Bending Radius Static	11.0 mm
Weight	0.06 kg

Environmental data

Operation Temperature Range	-40.0 $^{\circ}$ C ... 85.0 $^{\circ}$ C
-----------------------------	--