




REV.	DESCRIPTION/ECO NO.	DATE
	Released	3/24/21



NO TREATMENT, SUCH AS
APPLICATION OF FLUX,
SHALL BE DONE.


JKL PART NUMBER:

LAMP NUMBER: DW10

VOLTS RATED	AMPS $\pm 10\%$	*MSCP $\pm 25\%$	*LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
14	.100	.500	6.29	10,000	C2F

*LAMP RATING ONLY WITHOUT BASE

BASE COLOR: GRAY

METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION TITLE T-1 1/4 Neo Wedge Lamp				
	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0						
DRAWN BY L. WENGSTROM	APP'V'D BY SN 3/24/21	DATE	SIZE A	FSCM NO. 55335	DRAWING NO. DNW80-DW10/GRA		
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE	RELEASED DATE 3/24/21	REVISION DATE	REV. NO.	SHEET 1 OF 1