

Technical drawing of a mechanical part, likely a connector or plug, showing multiple views and dimensions. The drawing includes a top view, a side view, and two cross-sectional views.

Top View Dimensions:

- Overall width: 9.0
- Overall height: 4.3 ± 0.1
- Left side width: 4.0
- Right side width: 3.8
- Top left width: 1.1
- Top middle width: 1.7
- Top right width: 2.2
- Bottom left width: 1.1
- Bottom middle width: 1.7
- Bottom right width: 2.2
- Top left height: 0.043 ± 0.008
- Top middle height: 0.067 ± 0.008
- Top right height: 0.087 ± 0.008
- Bottom left height: 0.043 ± 0.008
- Bottom middle height: 0.067 ± 0.008
- Bottom right height: 0.087 ± 0.008
- Bottom left radius: 0.008
- Bottom middle radius: 0.008
- Bottom right radius: 0.008

Side View Dimensions:

- Overall length: 1.5
- Overall width: 0.059 ± 0.008
- Top width: 0.043 ± 0.004
- Bottom width: 1.1 ± 0.1

Cross-sectional View Dimensions:

- Overall width: 1.95 ± 0.008
- Overall height: 0.077 ± 0.002
- Top width: 0.077 ± 0.002
- Bottom width: 0.028 ± 0.004
- Bottom height: 0.7 ± 0.1

Other Dimensions:

- Overall length: 3.9 ± 0.15
- Overall width: 0.118 ± 0.002
- Top width: 3.0 ± 0.05
- Bottom width: 1.54 ± 0.006
- Bottom height: 0.169 ± 0.004
- Bottom radius: 0.110
- Bottom width: 2.8
- Bottom height: 0.098
- Bottom radius: 0.079
- Bottom width: 2.0
- Bottom height: 0.083
- Bottom radius: 2.1

WIRE BARREL

1. Unless otherwise specified, tolerances are $\pm 0.012/\pm 0.3$

2. Dimensions are in inch/mm.

UNCONTROLLED ISSUE

**THIS DRAWING/DOCUMENT IS THE
PROPERTY OF J.S.T. (U.K.) LTD. IT
MUST NOT BE COPIED OR USED FOR
MANUFACTURE WITHOUT WRITTEN
PERMISSION FROM J.S.T. (U.K.) LTD**

		CONTACT		PHOSPHOR BRONZE		COPPER-UNDERPLATED TIN-PLATED					
No.	NAME		MATERIAL		REMARKS		REVISIONS				
 J. S. T.								PART NAME		NH CONNECTOR	
								PART No.		BHF SHF-001T-0.8BS	
								DRAWING No.		KRD-10930	
APPROVED BY		CHECKED BY		DRAWN BY		SCALE		PROJECTION		DATE	
NH				Y.O		1/4		3rd		FEB. 21 1992	
										ISSUE	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO JST
AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

PI-E0023

0891011000 N