


JWPB CONNECTOR

2.0 mm/Wire-to-wire connectors (Waterproof type)



This JWPB connector can be used for the place of which especially waterproof is required.

This is the wire-to-wire connector that is grade 7 ingress protection of JIS C 0920 (IPX7 of IEC 60529).

- Waterproof performance
- Contained seal ring
- Solid rubber seal
- Double-spring construction
- Housing-to-terminal locks
- Inner-housing lock

Standards


⚡ : Recognized E60389

Ⓢ : R50326661

Specifications


- Current rating: 3 A AC/DC (AWG #22)
- Voltage rating: 100 V AC/DC
- Temperature range: -55°C to +85°C
(including temperature rise in applying electrical current)
- Contact resistance: Initial value/ 10 mΩ max.
After environmental tests/ 15 mΩ max.
- Insulation resistance: 1,000 MΩ min.
- Withstanding voltage: 1,000 VAC/minute
- Applicable wire: AWG #26 to #22
0.13 to 0.33 mm²
Insulation O.D./ 1.4 to 1.7 mm
- Waterproof grade: Grade 7 ingress protection of JIS C 0920 (IPX7 of IEC 60529)
- * In using the products, refer to "Handling Precaution for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.

Assembly layout




Contact

Tab contact



Receptacle contact



Model No.		Applicable wire		Insulation O.D. (mm)	Q'ty/reel
Tab contact	Receptacle contact	mm ²	AWG #		
SWPT-001T-P025	SWPR-001T-P025	0.13 to 0.33	26 to 22	1.4 to 1.7	8,200

Material and Finish

Tab contact: Phosphor bronze, tin-plated (reflow treatment)

Receptacle contact: Copper alloy, tin-plated (reflow treatment)

RoHS2 compliance

Note: Contact JST for brass products.











Contact	Crimping machine	Applicator	
		Crimp applicator	Crimp applicator with dies
SWPT-001T-P025	AP-K2N	MKS-L	APLMK SWPR/T001-025
SWPR-001T-P025			

Note: Contact JST for fully automatic crimping applicator.

JWPF CONNECTOR

Housing

Material: PBT, UL94V-0, natural (white)

No. of circuits	Tab housing (for Tab contact)		Receptacle housing (for Receptacle contact)	
2	02T-JWPF-VSLE-S 	Q'ty/ bag 1,000	02R-JWPF-VSLE-S 	Q'ty/ bag 1,000
3	03T-JWPF-VSLE-S 	Q'ty/ bag 1,000	03R-JWPF-VSLE-S 	Q'ty/ bag 1,000
4	04T-JWPF-VSLE-S 	Q'ty/ bag 1,000	04R-JWPF-VSLE-S 	Q'ty/ bag 1,000
6	06T-JWPF-VSLE-D 	Q'ty/ bag 1,000	06R-JWPF-VSLE-D 	Q'ty/ bag 1,000
8	08T-JWPF-VSLE-D 	Q'ty/ bag 1,000	08R-JWPF-VSLE-D 	Q'ty/ bag 1,000

RoHS2 compliance

Note: 1. Tab housing comes with seal rubber plate, seal ring and seal ring holder.
2. Receptacle housing comes with seal rubber plate.