



CONNECTION	
P1	COLOR
1	GRAY
2	GRAY/BLACKLINE

DIMENSIONS: mm

SPECIFICATIONS	
Operation Temperature	-10°C~+80°C
Insulation Resistance	DC/250V 5MΩ Min.
Withstand Voltage	AC/250V 5mA, For one minute
Continuity Test	100%
Continuity Resistance	3Ω Max.
Tensile Strength	DC/M/1.35x3.5 Overmold to cable shall withstand 3Kgf pull min for minute
RoHS Compliant	