






Rating	15A 250V AC		Mounting Hole
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Fuse Size	$\phi 6.35 \times 30\text{mm}$ $\phi 6.35 \times 31.8\text{mm}$		



Material:
Housing: Black, PF
Cover: Black, PBT
Terminals: Nickel Plated Brass



Tolerances ± 0.3 Unless Otherwise Specified

									△
									△
Date	Name		Description					No.	
Drawn	Checked	Approved	SCI BOM No.	1310935	Model Name	FUSE HOLDER			
袁浩徐		<i>Simon</i>	Customer No.	112-R3-44CA	Model No.	R3-44CA		Rev.	
09/24/19		10/8-19	Unit	mm	Shin Chin Industrial Co., Ltd.				0