


Date	Name	Description	No.
			△
			△



Shaft Hole $\phi 6.4$

Tolerances $\pm 0.3\text{mm}$ Unless Otherwise Specified

4	Cover	1	ABS	Blue		
3	Screw	1	Brass alloy	M3*P0.5*3L		
2	Metal insert	1	Brass alloy	$\phi 8*8\text{L}*\phi 6.4$		
1	Housing	1	PF	Black		
No	Description	Q'ty	Material	Specification	Finish	Remark
Drawn	Checked	Approved	SCI BOM No.		Model Name	CONTROL KNOBS
袁浩徐			Customer No.	112-RN-118F-BL/6.4	Model No.	RN-118F-BL
03/05/'20			Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. X0