


R13-424



Rating

6A 125V AC
3A 250V AC

Contact resistance

50mΩ Max


Insulation resistance

DC 500V 100MΩ Min

Dielectric strength

AC 1000V 1 minute

Cut-out



4 mm max

FEATURES

- * MATERIAL: Metal lever is nickel plated metal. Bushing is nylon (UL flame: 94V-2). Base is phenolic.
- * Indicator plate is optional.
- * Watertight boot (W-70B) is optional only for lever #1.

R13-424


FUNCTION

A



LEVER

1



2



TERMINAL

0 5 T SO

0 8 SC 6-32UNC

1 1 WIRE

