



DIMENSIONS: mm (in.)

**Electrical Specifications:**

- Rating: 3A/125VAC; 1.5A/250VAC
- Contact Resistance: 50m Ω Max.
- Insulation Resistance: 500VDC 100M Ω Min.
- Dielectric Strength: 1000VAC for 1 Minute

Note:

- RoHS Compliant by Exemption

Shin Chin Part No.	Type	Circuit
R13-40A-05-BB	2P SPST	Off-(On)
R13-40A-05-BR	2P SPST	Off-(On)
R13-40B-05-BB	2P SPST	Off-On
R13-40B-05-BR	2P SPST	Off-On

**Pushbutton Switches**

R13-40A-05-BB, R13-40A-05-BR,
R13-40B-05-BB, R13-40B-05-BR