




Rating	3A 125V AC 1A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P SPST OFF-ON		






Material:

Bottom: Red, PF

Housing: Black, ABS

Button: ABS

Printed: None



Tolerances ± 0.3 Unless Otherwise Specified

09/02/'21	曾敏捷	依ECR(RAD20210824-393)外觀圖恢復刻字標示,去除刻字圖號標示					△	
05/10/'21	曾敏捷	外觀圖取消安規標示,增加刻字圖號標示					△	
11/12/'13	Ruby	依品管清查安規,RU兩側須加標"C"與"US"					△	
Date		Name		Description			No.	
Drawn		Checked	Approved	SCI BOM No.	1830256	Model Name	PUSH SWITCH	
曾敏捷		符列迎	李理	Customer No.		Model No.	R13-83B-05	Rev.
09/02/'21		2021/09/11	2021/09/11	Unit	mm	Shin Chin Industrial Co., Ltd.		3