


R13-416



Ø 12.2
5 mm max

30A 12V DC
10A 24V DC

FEATURES

* Watertight boot (W-70A) is optional for lever #1 (refer page 85).



FUNCTION



LEVER

1 Metal Lever



2 Plastic Lever



6 Plastic Lever



TERMINAL

0 1 .250" SQ

0 5 S0

0 6 SC M3

0 7 SC M4

7 Plastic Lever



R13-416C1-01



R13-416A2-01



R13-416C6-01



R13-416D7-01