



Rating	10A
Insulation Resistance	DC 500V 100M ohm Min.
Voltage Breakdown	AC 500V 1 minute
Operation Temperature	-20°C~80°C
Color	Black

Material:
Metal Clip: nickel plated SPCC
Plastic Cover: PVC , Black

*.Clamping force 2.5kgf at 8 mm(A)

*.Clamping force 300g±50g when clamped 12 AWG wire



Tolerances Unless Otherwise Specified ±0.5

								△
								△
Date	Name		Description					NO
Drawn	Checked	Approved	SCI BOM No.	153010Z	Model Name	ALLIGATOR CLIPS		
林明呈			Customer No.	112-R8-91-B	Model No.	R8-91-B		Rev.
5/16/19			Unit	mm	Shin Chin Industrial Co., Ltd.			0