


# DC Power Jack for Laptop

163-0210-E, 163-0212-E



DC Power Jack for Laptop



Dimensions: mm (In.)

Part No.	
163-0210-E	A
163-0212-E	B

TOLERANCE	
X.	±0.5
X.X	±0.3
X.XX	±0.15

ELECTRICAL SPECIFICATIONS	
Rated Voltage:	12VDC 1A
Insulation Resistance:	100M ohm 500VDC
Voltage Withstand:	500VAC 1 min.
Operating Temperature:	-25°C to +85°C

MATERIAL SPECIFICATIONS			
Name	Material	Plated	Color
Housing	PBT	---	Black
Center Pin	Brass	Nickel	---
Tip	Copper Alloy	Tin	---
Tip Shunt	Brass	Tin	---
Sleeve	Brass	Tin	---
RoHS Compliant			

Date Last Revised: 06-12-06

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300975

163-0210-E, 163-0212-E