



CONNECTION	
P1	COLOR
1	INJECT WHITE
2	BLACK

DIMENSIONS: mm

SPECIFICATIONS	
Operation Temperature	-10°C~+80°C
Insulation Resistance	DC/250V 5MΩ Min.
Withstand Voltage	AC/250V 5mA, For one minute
Continuity Test	100%
Continuity Resistance	3Ω Max.
Tensile Strength	DC jack overmold to cable jacket shall withstand 2kgf pull min. for one minute.
RoHS Compliant	

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301450

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.