


DIMENSIONS: mm



Specifications:

- Operating Temperature: $-10^{\circ}\text{C} \sim +80^{\circ}\text{C}$
- Insulation Resistance: DC/250V, $5\text{M}\Omega$ Min.
- Withstand Voltage: AC/250V 5mA For One Minute.
- Continuity Test: 100%
- Tensile Strength: DC Plug overmold to cable shall withstand 3Kgf pull min. for one minute.

Notes:

- RoHS Compliant