



DIMENSIONS: mm



SCHEMATIC



SPECIFICATIONS

Contact Resistance:	30mΩ Max.
Insulation Resistance:	100MΩ Min. at DC 500V
Dielectric Withstand Voltage:	AC 500V for 1 minute
RoHS Compliant	

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301510

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.