




NOTE :

1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	22	20	18	16
AMP.	3	4	7	10
2. WIRE RANGE : 22-16 A.W.G. (0.5-1.5 mm²)
3. NEMA TAB : 0.032 inch * 0.187 inch (0.8 mm * 4.75 mm)
4. SURFACE TREATMENT : TIN PLATED
5. THICKNESS : 0.4 mm

Tolerance Unless Otherwise Specified		
0 > 6 mm	± 0.20	ANGLE
6 > 18 mm	± 0.30	0° > ° REF ±
18 > 30 mm	± 0.40	° > ° ±
30 > 75 mm	± 0.50	° > ° ±

NAME	NON-INSULATED MALE DISCONNECTORS			UNIT	791	⊕	⊖
PART NO.	MDN1-187(8)	MATERIAL	BRASS	APPROVE	張馨尹		
NUMBER	KT-96455-C	SCALE	SHEET	PAGE	CHECKED	楊駿孝	
DATE	2007/07/23	4/1	1-0	10F2	DRAWN	張馨尹	

KST. K.S. TERMINALS INC.