

QUICK SPLICE CONNECTORS







MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12
AMP.	9	12	17	18	30	35

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: NYLON

TERMINAL MATERIAL: PHOSPHOR BRONZE

ITEM NO.	WIRE RANGE A.W.G. mm ²	Suggested Mate With Male Tab (Thickness X Width)	W inch mm	L inch mm	COLOR	FIGURE	TYPE CONNECTOR	Q'TY BOX
878006D	22-18 A.W.G. 0.5-0.75 mm ²	MDFNY1-250 (.032X.250)	.366 9.3	1.583 40.2	RED	DOUBLE CRIMP 		500
878106D	18-14 A.W.G. 0.75-2.5 mm ²	MDFNY2-250 (.032X.250)	.366 9.3	1.583 40.2	BLUE	DOUBLE CRIMP 		500
878206D	12 A.W.G. 4 mm ²	MDFNY5-250 (.032X.250)	.366 9.3	1.583 40.2	YELLOW	DOUBLE CRIMP 		500

  ALL LISTED