


NYLON-INSULATED (STRAIGHT) BUTT SPLICE CONNECTORS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10	8	6	4	2
AMP.	9	12	17	18	30	35	50	70	95	125	170

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

CONNECTOR MATERIAL: COPPER INSULATION MATERIAL: NYLON

INSULATION COLOR:

22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■
8 A.W.G.: RED ■ 6 A.W.G.: BLUE ■ 4 A.W.G.: YELLOW ■ 2 A.W.G.: RED ■

WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION inch mm			MATERIAL	CRIMPING TOOL	Q'TY BOX
		L	D	d1			
22-16 A.W.G. 0.5-1.5 mm ²	BNY1	1.063 27.0	.126 3.2	.067 1.7	COPPER PLATE	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	BNY2	1.063 27.0	.150 3.8	.091 2.3	COPPER PLATE	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
12-10 A.W.G. 4-6 mm ²	BNY5	1.063 27.0	.209 5.3	.134 3.4	COPPER PLATE	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500