

DIN 46237

NYLON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	6	4	2	1/0
AMP.	95	125	170	230


MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: NYLON

INSULATION COLOR:

6 A.W.G.: BLUE 4 A.W.G.: YELLOW 2 A.W.G.: RED 1/0 A.W.G.: BLUE

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION mm						CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		d3	l	d1	d4	a	S		
6 A.W.G. 16 mm ²	DRNYB5-16		#10	5.3	11.0	31.5	5.8	11.0	21.5	1.2	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/16 OR K.S. MODEL KS-HDC38A WITH DIE INDEX NO.:14(INS)	250
	DRNYB6-16		1/4	6.5								250
	DRNYB8-16		5/16	8.4	14.0	33.5						250
	DRNYB10-16		3/8	10.5	18.0	35.5						250
	DRNYB12-16		1/2	13.0	22.0	37.5						250
4 A.W.G. 25 mm ²	DRNYB5-25		#10	5.3	12.0	38.0	7.5	13.0	24.0	1.5	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/25 OR K.S. MODEL KS-HDC38A WITH DIE INDEX NO.:22(INS)	100
	DRNYB6-25		1/4	6.5								100
	DRNYB8-25		5/16	8.4	16.0							100
	DRNYB10-25		3/8	10.5	18.0	39.0						100
	DRNYB12-25		1/2	13.0	22.0	44.0						100
	DRNYB16-25		5/8	17.0	28.0	48.0						100
2 A.W.G. 35 mm ²	DRNYB6-35		1/4	6.5	15.0	41.0	9.0	14.5	27.0	1.6	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/35 OR K.S. MODEL KS-HDC38A WITH DIE INDEX NO.:38(INS)	100
	DRNYB8-35		5/16	8.4	16.0							100
	DRNYB10-35		3/8	10.5	18.0	42.0						100
	DRNYB12-35		1/2	13.0	22.0	46.0						100
	DRNYB16-35		5/8	17.0	28.0	51.0						100
1/0 A.W.G. 50 mm ²	DRNYB6-50		1/4	6.5	18.0	47.5	11.0	16.5	29.5	1.8	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/50	50
	DRNYB8-50		5/16	8.4								50
	DRNYB10-50		3/8	10.5								50
	DRNYB12-50		1/2	13.0	22.0	49.5						50
	DRNYB16-50		5/8	17.0	28.0	53.5						50

UL cUL ALL LISTED