

VINYL-INSULATED LIPPED BLADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50


MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: VINYL

INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.		DIMENSION ^{inch} mm								CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	W	F	L	E	D	d1	A	T		
22-16 A.W.G. 0.5-1.5 mm ²	LBVB1-3	LBV1-3	.118 3.0								IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
	LBVB1-4.6	LBV1-4.6	.181 4.6	.685 17.4	1.071 27.2	.394 10.0	.157 4.0	.067 1.7	.083 2.1	.030 0.75		1000
16-14 A.W.G. 1.5-2.5 mm ²	LBVB2-3	LBV2-3	.118 3.0								IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
	LBVB2-4.6	LBV2-4.6	.181 4.6	.685 17.4	1.071 27.2	.394 10.0	.177 4.5	.091 2.3	.083 2.1	.031 0.8		1000
12-10 A.W.G. 4-6 mm ²	LBVB5-3	LBV5-3	.118 3.0						.110 2.8		IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500
	LBVB5-4.6	LBV5-4.6	.181 4.6	.677 17.2	1.189 30.2	.512 13.0	.252 6.4	.134 3.4		.039 1.0 .108 2.75		500

UL cUL ALL LISTED