


NYLON-INSULATED DOUBLE CRIMP LOCKING SPADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON
INSULATION COLOR:

 22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■
DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL
TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION ^{inch} mm							CRIMPING TOOL	Q'TY BOX
		d2		W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	LSNYD1-3.2	#4	.126 3.2	.252 6.4	.256 6.5	.866 22.0	.433 11.0	.177 4.5	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000B WITH DIE INDEX COLOR:RED	1000
	LSNYD1-3.7	#6	.146 3.7									1000
	LSNYDS1-4	#8	.169 4.3	.283 7.2								1000
	LSNYDL1-4	#8	.169 4.3	.319 8.1								1000
	LSNYDS1-5	#10	.209 5.3									1000
	LSNYDL1-5	#10	.209 5.3									.374 9.5
16-14 A.W.G. 1.5-2.5 mm ²	LSNYD2-3.2	#4	.146 3.7	.236 6.0	.256 6.5	.866 22.0	.433 11.0	.205 5.2	.091 2.3	.031 0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000B WITH DIE INDEX COLOR:BLUE	1000
	LSNYD2-3.7	#6	.146 3.7									1000
	LSNYDL2-3.7	#6	.146 3.7	.283 7.2								1000
	LSNYD2-4	#8	.169 4.3									1000
	LSNYDL2-4	#8	.169 4.3	.319 8.1								1000
	LSNYDS2-5	#10	.209 5.3									1000
	LSNYDL2-5	#10	.209 5.3									.366 9.3
	LSNYD2-6	1/4	.209 5.3	1000								
12-10 A.W.G. 4-6 mm ²	LSNYDS5-3.7	#6	.146 3.7	.307 7.8	.276 7.0	.992 25.2	.512 13.0	.276 7.0	.134 3.4	.039 1.0	IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000B WITH DIE INDEX COLOR:YELLOW	500
	LSNYD5-3.7	#6	.146 3.7									500
	LSNYD5-4	#8	.169 4.3	.327 8.3								500
	LSNYD5-5	#10	.209 5.3	.354 9.0								500
	LSNYD5-6	1/4	.252 6.4	.472 12.0								500

UL cUL ALL LISTED