

DATA SHEET.


DEFINITIVE [X]
FILTER CODE: PROVISIONAL []

APPROVALS:

F.LL.D3.030A.AN.I9A

CIRCUIT DIAGRAM:

ELECTRICAL SPECIFICATIONS:




RATED VOLTAGE : 460Vac, 50/60Hz. 10% fluctuation in voltage supply accepted.
RATED CURRENT : 30 Amps max.
LEAKAGE CURRENT : 11mA max @ 460Vac, 50Hz.
CLIMATIC CATEGORY : HPF (25/085/21)
LINE TO LINE CAPACITORS : 9 x 2.2uF(X2) MKT.
LINE TO GROUND CAPACITORS: 2 x 47nF(Y).
LINE INDUCTANCE : 4.5mH per phase.
LINE RESISTANCE : < 20 milliohms
VOLTAGE PROOF : Line to Line: 1700Vdc, 2 sec
Lines to Ground: 2700Vdc, 2 sec.

MECHANICAL SPECIFICATIONS:

MANUFACTURE: Tin plated steel enclosure and lid. Electrical components sealed with self-extinguishing resin.

CONNECTIONS: All connections M5 threaded terminals with nuts and washers.

DIMENSIONS: (mm).



Approved, seen & subscribed

ISSUE: 1.
DATE: 1st October 1997.

COMPILED BY: D.Morrison.

.....
Customer's stamp and signature.