

Power Adapters



Model P/N	Wattage	DC Voltage Output	DC Current Output	Outline L*W*H (mm)	AC Inlet	Pin @ (0 Amps)	Avg-Eff.	DC Cable L (mm) / D (AWG)
PA-1050-2L	5	5	1	41*29*23	Wall Mount	<=0.1W	>73.6%	NA
PA-1100-22L	10	5	2	49*37*24	Wall Mount	<=0.1W	>78.4%	NA
PB-1080-2SA0	7.5	5	1.5	80*43.5*30	Wall Mount	<=0.3W	>=72%	1830/20
PB-1120-8SA0	12	12	1	89.3*36*49.5	Wall Mount	<=0.3W	>=77.8%	1500/24
PB-1150-8M00	15	12	1.2	89.3*36*49.5	Wall Mount	<=0.3W	>=81%	1500/24
PB-1180-1M00	18	12	1.5	89.3*36*49.5	Wall Mount	<=0.3W	>=81%	1500/24
PB-1240-6SA0	24	12	2	112*52*31	C8	<=0.3W	>=82.1%	1500/20
PA-1360-5M00	36	12	3	126.5*50*30.6	C8	<=0.3W	>=84.6%	1830/18
PA-1041-71IL-LF	40	12	3.33	108*48*30	C14	<=0.1W	>=85.3%	1050/20
PA-1061-01IL-LF	60	12	5	120*60*35	C14	<=0.3W	>=87%	1500/16
PA-1061-02IL-LF	60	12	5	135*60*35	C14	<=0.3W	>=87%	1500/16
PA-1081-01LT-LF	80	12	6.67	150*60*35	C14	<=0.3W	>=87%	1500/14
PA-1041-91AM-LF	40	19	2.1	108*48*30	C14	<=0.15W	>=85.5%	1050/20
PA-1051-91A1-LF	50	19	2.63	108*48*30	C6	<=0.1W	>=87%	1500/20
PA-1650-64AM-LF	65	19	3.42	107*48.7*30.5	C8	<=0.1W	>=86.5%	1500/18
PA-1650-86AW	65	19	3.42	95*50*25.4	C6	<=0.3W	>=87%	1800/20
PA-1900-32P1	90	19	4.74	127*51*30	C6	<=0.2W	>=88%	1800/18

Applications

Computer

- * Notebook and Desktop
- * Printer
- * Tablet



Consumer

- * Entertainment Game Station
- * Plasma Display Panel
- * Digital recorder



Communication

- * Cellular Mobile Phone
- * USB Hub
- * Network Switching Hub



Leadtime

16 weeks

Specifications and Safety Certifications

Available Upon Request