


Dimensions: mm (in.)



SWITCH FUNCTION

POS.1	POS.2
ON	(ON)
2-3,5-6	2-1,5-4

Electrical Specifications:

- Electrical Life: 40,000 make-and-break cycles at full load
- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@ sea level.
- Rating: 2A / 250 VAC
5A / 120 VAC or 28 VDC

Mechanical Specifications:

- Operating Temperature: -30° C to +85° C.

Materials:

- Case: Diallyl phthalate (DAP)
- Acuator: Brass, chrome plated.
- Bushing: Brass, nickel plated.
- Housing: Stainless steel.
- Terminal/Contact: Silver or Gold plated.
- Switch Support: Brass, Tin plated.

Note:

- RoHS compliant by exemption

Toggle Switch
108-1MD2T1B1M1QE-EVX

Mountain
Switch