

9050.0100

Product number

Actuation type	direct	
Weight	6.800 g	
Switching function	Changeover switch (SPDT momentary)	
Number of poles	1 - pole	
Connections	Solder terminal, sealed	
Mechanical life endurance	1E5	
Contact system	25E3	
Rating IEC	5 A 48 V AC 4 A 30 V DC	
Contact resistance (new condition)	< 20 mOhm	
Insulation resistance (new condition)	> 1000 MOhm	
Voltage strength at 250 V	Function insulation / Basic insulation	null V
	Reinforced insulation	null V
	Small contact distance	> 1000 V
Actuators	actuator, CurZn nickel-plated	
Housing description	base plate: olivegreen threaded socket: CnZn nickel-plated, hexagonal nuts of nickel-plated CuZn toothed disc: Duroplast (base) / chromated galvanized steel (bracket plate) bracket plate: stainless steel	
Connection surface	Bearing connection	silver plated
	External connection	silver plated

Contact material	Ag
Contact type	lifting contact
Miscellaneous	stroke 1.8 mm corresponding pushbuttons 9090.03.. see additional parts
Type of fastening	central fastening M6 x 0.75

All information subject to possible technical changes