

9051.0100

Product number

Weight	6.300 g	
Switching function	Changeover switch (SPDT)	
Number of poles	1 - pole	
Connections	Solder terminal, sealed	
Mechanical life endurance	1E5	
Contact system	25E3	
Rating IEC	5 A 48 V AC 4 A 30 V DC	
Contact resistance (new condition)	< 20 mOhm	
Insulation resistance (new condition)	> 1000 MOhm	
Voltage strength at 250 V	Function insulation / Basic insulation	null V
	Reinforced insulation	null V
	Small contact distance	> 1000 V
Actuators	actuator, CuZn nickel-plated	
Housing description	threaded socket: CuZn nickel-plated, hexagonal nuts of nickel-plated CuZn base plate: olivegreen bracket plate: stainless steel toothed disc: Duroplast (base) / chromated galvanized steel (bracket plate)	
Connection surface	Bearing connection	silver plated
	External connection	silver plated
Contact material	Ag	

Contact type	lifting contact
Miscellaneous	corresponding pushbuttons 9090.03.. see additional parts stroke 3.8 mm
Type of fastening	central fastening M6 x 0.75

All information subject to possible technical changes