

9055.0200

Product number

Actuation type	direct	
Weight	6.100 g	
Switching function	Changeover switch (DPDT)	
Number of poles	2 - pole	
Connections	Solder terminal, sealed	
Mechanical life endurance	1E5	
Contact system	1E5	
Rating IEC	4 A 30 V DC 5 A 48 V AC	
Contact resistance (new condition)	< 20 mOhm	
Insulation resistance (new condition)	> 1000 MOhm	
Voltage strength at 250 V	Function insulation / Basic insulation	null V
	Reinforced insulation	null V
	Small contact distance	> 1000 V
Actuators	tappet, CurZn nickel-plated	
Housing description	bracket plate: stainless steel base plate: olivegreen	
Connection surface	Bearing connection External connection	silver plated silver plated
Contact material	Ag	

Contact type	lifting contact
Miscellaneous	corresponding cover frame 9090.11.. or rocker 9090.14.. see additional parts
Type of fastening	Snap fastening

All information subject to possible technical changes